



Worldwide Distribution by  
**FLASHSCAN.US**  
 Moving Image Tools and Technology  
 now found at [MovingImageTools.com](http://MovingImageTools.com)  
[Click here for](#) FXSYS PTR Information


European and Middle East Dealer  
**VISIBLE SPROCKETS**  
 Visible Sprockets, Ltd  
 Graham Collett  
<http://visible-sprockets.co.uk/contact.html>

FXSYS PTR End User Prices in US Dollars. Effective May 8, 2018 Contacts updated Oct 11, 2018

FXSYS Particle Transfer Rollers	Minimum Order	Each	12+	52+	Minimum Purchase (4)	12	52
1.5" x 35mm Micromat™	4	\$85.80	\$81.51	\$77.22	\$343.20	\$978.12	\$4,015.44
3" by 35mm Micromat™	4	\$79.56	\$75.58	\$71.60	\$318.24	\$906.98	\$3,723.41
1.5" x 70mm Micromat™	4	\$130.00	\$123.50	\$117.00	\$520.00	\$1,482.00	\$6,084.00
3" x 70mm Micromat™	4	\$88.92	\$84.47	\$80.03	\$355.68	\$1,013.69	\$4,161.46
<b>FXSYS Red Tacky™</b>							
1.5" x 35mm RT™	4	\$68.50	\$65.00	\$60.00	\$274.00	\$780.00	\$3,120.00
3" by 35mm RT™:	4	\$78.50	\$75.00	\$65.00	\$314.00	\$900.00	\$3,380.00
					0	0	0
					0	0	0

To order, please contact Ted Langdell at [Moving Image Tools and Technology](http://MovingImageTools.com) or Graham Collett at [visible-sprockets.co.uk](http://visible-sprockets.co.uk)

For Quantities of 100+ and Custom colors or other questions... Ask us!



These specially finished, *premium* PTRs have been the chosen PTR in post production facilities and with major film scanner manufacturers world-wide.

They are available in two diameters and two widths: 1.5" and 3" diameters and 35mm and 70mm widths

FXSYS MicroMat™ PTRs are made in controlled environment with a Durometer range of 28-34, which is ideal for use with motion picture film

FXSYS 3" x 35mm Green Micromat™ Particle Transfer Roller showing diamond-etched microgrooved surface which has what are like tiny tire treads that pick up and hold particulate matter.



FXSYS Tacky Red™ Particle Transfer Rollers which pick up more particle matter than the slightly harder MicroMat™ PTR

The FXSYS Tacky Red™ PTR has a softer durometer reading between 20-24. The softer, ungrooved tacky surface picks up even more material than the MicroMat™ Microgrooved PTR's and is usable until its covered with undesirable material.

Not for high-speed use.